



**Part Number :** [1300101729](#)

**Product Description :** Mini-Change A-Size Double-Ended Cordset, 4 Poles, Male (Straight) to Female (90°), 16 AWG, Yellow TPE Cable, 42.0m (137.80') Length

**Series Number :** 130010

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 114031K12M420

---

## Documents and Resources


### Drawings

[1300101729 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Phosphine oxide, diphenyl(2,4,6-trimethylbenzoyl) per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	130010
Description	Mini-Change A-Size Double-Ended Cordset, 4 Poles, Male (Straight) to Female (90°), 16 AWG, Yellow TPE Cable, 42.0m (137.80') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Double Ended
UPC	78172503839

### Agency

UL	E152210
----	---------

### Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	600V

### Physical

Cable Diameter	10.67mm (.420")
Cable Length	42.0m (137.80')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change

Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	44252.000/g
Orientation	90° to Straight
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	16

---

This document was generated on Apr 11, 2026