Part Number : 733581041
Product Description : Gang of 8 MPRF Jack, Standard, Right Angle, PCB Receptacle, Through Hole, 2.69mm Leg Length, Tray, 50 Ohms
Series Number : 73358
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

733581041_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

735970640-000.pdf

PS-89675-471-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 3; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73358
Description	Gang of 8 MPRF Jack, Standard, Right Angle, PCB Receptacle, Through Hole, 2.69mm Leg Length, Tray, 50 Ohms
Application	RF
Product Name	MPRF
Style	PCB
Type	Subminiature
UPC	887191544076

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	9.936/g
Orientation	Right Angle

Downloaded from Arrow.com.

Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
PCB Thickness - Recommended	2.40mm
Reverse Polar	No
Wire/Cable Type	N/A

Downloaded from Arrow.com.