

REV.		DATE		DESCRIPTION	
A		02/20/01		MODIFY MOUNT LEGS	

Technical drawing of a connector mount showing side and top views with dimensions in inches and millimeters.

Side View Dimensions:

- Top Flange Width: 9.5 [.374]
- Top Flange Thickness: 3.5 [.138]
- Body Width: 6.5 [.256]
- Body Height: 6.5 [.256]
- Mount Leg Width: 2.75 [.108]
- Mount Leg Thickness: .76 [.030]
- Mount Leg Height: .96 [.038]

Top View Dimensions:

- Overall Width: 6 [.237]
- Overall Height: 4.5 [.177]
- Mount Leg Width: 4.22 [.166]

DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN () ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		APPROVALS		DATE	Connex Connector Corporation TITLE MCX R/A PCB SURFACE MOUNT RECEPT. SIZE A FSCN NO. 99001 DWG. NO. 252149.DWG REV. A			
1 BODY	BRASS	GOLD	DRAWN	G.R.S.	02/20/01						
2 INSULATOR	TEFLON	NATURAL	CHECKED								
3 CONTACT PIN	BER. COPPER	GOLD	ISSUED								
4			UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:								
5			0.5-6 = ± 0.2								
6			6-30 = ± 0.4								
7			30-120 = ± 0.6								
8			120-315 = ± 1								
			315-1000 = ± 1.6								
			1000-2000 = ± 2.4								
			DO NOT SCALE DRAWING								
					SCALE		NA		PART NO.		
							252149		SHEET		
							1		OF 1		