




Home > Products > MICRO SWITCH™ Toggle Switches > TL > Product Page

### 4TL887-2D



Actual product appearance may vary.

**TL Series Toggle Switch, 4 pole, 2 position, Screw terminal, Locking Lever**

#### ▼ Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

#### Features

Environment-proof sealing  
1,2, and 4 pole circuitry  
Standard and pull-to-unlock levers  
2 and 3 position, maintained and momentary toggle action  
Temperature range: -85° F to +160° F  
Completely sealed switching chamber  
Step-design case provides added space between terminals to help prevent shorting  
UL recognized, CSA certified  
CE approved

#### Potential Applications

Industrial machinery and equipment  
Military and commercial aviation  
Construction equipment  
Test instruments  
Agricultural machinery  
Process control  
Medical instrumentation

#### Description

MICRO SWITCH™ TL Series toggle switches have high strength, temperature resistant, non-tracking case material and silver cadmium oxide contacts. Pull-to-Unlock toggle levers prevent accidental operation; the lever must be pulled approx. 2,3 mm (0.09 inches) to change positions.

#### Supporting Documentation

[Accessory: Seals](#)

[Accessory: Nuts](#)

[Engineering Drawing](#)

Product Specifications			
Circuitry/Operating action	Keyway Position	Opposite Keyway Position	
	3 2	3 2	
	6 5	6 5	
	9 8	9 8	
	12 11	12 11	
	OFF	ON	
Product Type	MICRO SWITCH™ Toggle Switch		
Lever Lock	 Locked out of center position		
Ampere/Voltage Range (Resistive Load)	0.5 A at 250 Vdc, 0.75 A at 115 Vdc, 0.5 A to 20 A at 0.5 Vdc to 28 Vdc, 0.5 A to 15 A at 0.5 Vac to 277 Vac		
Circuitry	4PST		
Action	2 position		
Mounting	Bushing 15/32 in		
Termination	Screw		
Lever Type	Locking		
UL/CSA Rating Code	L191: 15 A - 125, 250, 277 Vac; 1/2 Hp - 125 Vac; 1 Hp - 250, 277 Vac; 5 A - 120 Vac "L"		
Comment	Gold plated contacts, no spring clip		
Availability	Global		
UNSPSC Code	30211908		
UNSPSC Commodity	30211908 Toggle switches		
Series Name	TL		

#### Keyword Search

Search for product and support information.

All Sensing and Control

#### Product Search

Part number search:

Use (\*) to expand search

#### Specification Search