

WI-M-14-XX-@

(Extra Heavy-Duty 14 AWG, UL Recognized, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-14-@ is 14 AWG, 420/0.08 stranded, tinned copper wire with highly flexible 4.7mm diameter silicone jacket.
 - Ratings:

Voltage	1100V
Dielectric Strength	3.2 KV/Min
Spark Test	10 KV
Rated Temperature	-40°C to 180°C
Temperature Rating	FT2
UL Recognition	3640
 - Length: The "XX" in the model number indicated length in feet.
Standard lengths: 10', 25', 30', 50', and 100'
 - Color: The "@" in the model number represents color.
Available colors: -0 Black, -2 Red