Product Families

- Automation
- Hazardous Location
- Industrial Components
- LED Lighting & Signaling
- Machine Safety
- Sensing

CW4B-M1E10G
Pushbutton 22MM 1NO Green







Add to Cart

Key Features

- ø22.3mm mounting hole compliant with IEC 60947-5-1
- 3.5-mm operator travel for pushbuttons ensures comfortable and reliable operation
- Black and metallic bezels available
- Illuminated pushbuttons, pushbuttons, pilot lights, selector switches and key selector switches are available
- Direct opening NC contact
- 10A contact rating; up to three contact blocks for non-illuminated and two contact blocks for illuminated models can be connected
- Up to 6 contacts per switch
- UL Type 4X rating

Specifications | Literature | Downloads

Product Type	Pushbutton
Mounting Hole Size	22mm
Shape	Round
Color	Green
Contact Rating	10A
Normally Open Contacts	1
Normally Closed Contacts	0
Ingress Protection Rating	IP65 degree of protection (IEC 60529) from panel front
Operation Type	Momentary

© 2018 IDEC Corporation All rights reserved. Use of, and copying from, this site is subject to our terms conditions.

Downloaded from Arrow.com.