




REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
C	ECN2022152	UPDATE FRAME	Abner 2022-09-28	Staven 2022-09-28	Sam 2022-09-28



NOTES:


1. MATERIAL:PHOSPHOR BRONZE;
2. FINISH: GOLD FLASH SURFACE PLATING OVER SOLDER AREA, Ni 40-120u" UNDER PLATING OVER ALL.
3. ALL MATERIAL MUST BE COMPLY WITH RoHS2.0;
4. WITH"▼"MUST BE CPK CONTROL.




3D VIEW

PUNCH DIRECTION&BURRS DIRECTION

RECOMMEND PCB LAYOUT
TOLERANCE: ±0.05mm

UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION		 Amphenol Aorora Technology (Huizhou) Co.,Ltd			
X.	±0.30	X. °	± 5'			TITLE: H3.4 CLIP			
X.X	±0.25	X.X °	± 4'						
X.XX	±0.20	X.XX °	± 3'	DOC TYP Customer Drw		REV.			
X.XXX	±0.15	X.XXX °	± 2'	DRAWN DATE					
LINEAR DIMS		ANGLES DIMS		Deming Li 2016-02-17		PART NUMBER: Z00U-4B7C1-11000			
DWG NO.: A-S0310				DESIGN DATE					
MATERIAL		SEE NOTES		Deming Li 2016-02-17		A4			
FINISHED		SEE NOTES		CHECKED DATE					
				Qi Han 2016-02-17		SCALE			
				APPROVED DATE					
				Hongkui Liu 2016-02-17		1:1		UNIT : mm	
						SHEET 1		OF 1	


1. PACKING INTO REEL:



NOTES:

- MATERIAL:
 - CARRY TAPE:PS,T=0.4mm,COLOR:TRANSPARENT.
 - REEL:HIPS,BLUE.
 - SHIM:PE,CLEAR.
- PRIMARY PACKING:2200PCS/REEL.
- SECONDARY PACKING:10REELS/CARTON(22000PCS/CARTON).
- PEELING RESISTANCE: 0.1N~0.9N(10~90gf);
PEELING ANGLE: 165°~180°;
PEELING SPEED: 300mm/minutes.
- NET WEIGHT: 0.093g
- CATON GROSS WEIGHT: 7.4Kg, NET WEIGHT: 2.05Kg


2. PACKING INTO CARTON:



REV.	ECR/ECN	No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
C			New specifications	Staven 2019-03-04	Peng Li 2019-03-04	Judy 2019-03-04
D			UPDATE FRAME	Abner 2022-05-24	Staven 2022-05-24	Sam 2022-05-24

TABLE:

NO.	Sketch Map	Difference
Z002-4B7C1-11000		H3.4 Gap0.1mm
Z00U-4B7C1-11000		H3.4 Gap0.3mm
Z017-4G7C1-11000-E200		H3.4 Gap0.3mm Chipped

UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION		 Amphenol Aorora Technology (Huizhou) Co.,Ltd						
X.	±0.30	X. °	± 5'									
X.X	±0.25	X.X °	± 4'									
X.XX	±0.20	X.XX °	± 3'									
X.XXX	±0.15	X.XXX °	± 2'									
LINEAR DIMS		ANGLES DIMS		DOC TYP Assembly Drw		TITLE: H3.4 CLIP						
				DRAWN	Abner	SIZE A4			PART NUMBER: SEE TABLE		REV. D	
				DATE	2022-05-24							
				DESIGN	Abner							
				DATE	2022-05-24							
DWG NO.: A-H0167				CHECKED	Staven							
MATERIAL		SEE NOTES		DATE	2022-05-24							
FINISHED		SEE NOTES		APPROVED	Sam	SCALE		1:1	UNIT : mm	SHEET 1 OF 1		
				DATE	2022-05-24							