

UC-EMLP (17X15) - Plastic label



0827885

<https://www.phoenixcontact.com/us/products/0827885>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, lettering field size: 17 x 15 mm, Number of individual labels: 8



Your advantages

- The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK printing system
- The UC-EMLP ... UniCard marking range includes self-adhesive device markers with good adhesive properties
- The sheets provide additional space for project information and function text that can be helpful during further assembly
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

Item number	0827885
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG10
Product key	BG2417
Catalog page	Page 298 (C-3-2019)
GTIN	4046356461092
Weight per piece (including packing)	8.498 g
Weight per piece (excluding packing)	7.078 g
Customs tariff number	39269097
Country of origin	PL

UC-EMLP (17X15) - Plastic label



0827885

<https://www.phoenixcontact.com/us/products/0827885>

Technical data

Product properties

Product type	Device marking
--------------	----------------

Marking

Number of individual labels	8
Number of individual labels per row	2
Identification technology	UV LED technology

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

RoHS compliant	yes
Adhesive strength	250 µm
Adhesive	Acrylic
Color	white
Material	PA
Flammability rating according to UL 94	V2
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

UC-EMLP (17X15) - Plastic label



0827885

<https://www.phoenixcontact.com/us/products/0827885>

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Dimensions

Width	17 mm
Text field width	17.00 mm
Text field height	15.00 mm
Length	15 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

UC-EMLP (17X15) - Plastic label



0827885

<https://www.phoenixcontact.com/us/products/0827885>

Classifications

ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UC-EMLP (17X15) - Plastic label



0827885

<https://www.phoenixcontact.com/us/products/0827885>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>



Accessories

BLUEMARK ID - Printer

1003334

<https://www.phoenixcontact.com/us/products/1003334>



Monochrome printer with UV LED technology and integrated "MARKING system app" identification software. 7" touch color display for printing plastic tags in UC, UCT, US, and UM format, as well as metal labels.

BLUEMARK ID COLOR - Printer

1002329

<https://www.phoenixcontact.com/us/products/1002329>



CMYK multicolor printer with UV LED technology, with integrated "MARKING system app" identification software, 7" touch color display for printing plastic tags in UC, UCT, and UM format, as well as metal labels.

UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>




PLOTMARK - Marking plotter

0804499

<https://www.phoenixcontact.com/us/products/0804499>

Marking plotter for the entire portfolio of UC marking materials and materials in sheet and strip format.




CMS-P1-PLOTTER - Marking plotter

5144615

<https://www.phoenixcontact.com/us/products/5144615>

Marking plotter, weight: 8 kg, length: 0.66 m, width: 440 mm, height: 125 mm, color: silver



UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>



BM ID-CARTR. BK - Ink cartridge

1044345

<https://www.phoenixcontact.com/us/products/1044345>

Replacement UV fluid, 23 ml, color: black



BM ID-CARTR. CY - Ink cartridge

1044346

<https://www.phoenixcontact.com/us/products/1044346>

Replacement UV fluid, 23 ml, color: cyan



UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>



BM ID-CARTR. YE - Ink cartridge

1044348

<https://www.phoenixcontact.com/us/products/1044348>



Replacement UV fluid, 23 ml, color: yellow

BM ID-CLEANING CARTR. - Cleaning cartridge

1044350

<https://www.phoenixcontact.com/us/products/1044350>



Replacement cleaning cartridge

UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>



BLUEMARK CLED-FLUID-CARTR. - Ink cartridge

5146662

<https://www.phoenixcontact.com/us/products/5146662>

Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge



BLUEMARK FLUID-CARTRIDGE - Ink cartridge

5147421

<https://www.phoenixcontact.com/us/products/5147421>

Cartridge, for replacement, 28 ml UV color, black including cleaning cartridge



UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>



CMS-DISPOSABLE-PEN 0,25 TR - Marker pen

5146685

<https://www.phoenixcontact.com/us/products/5146685>

Disposable pen, incl. adapter, integrated ink cartridge and pen station, writing thickness: 0.25 mm



CMS-DISPOSABLE-PEN 0,35 TR - Marker pen

5146686

<https://www.phoenixcontact.com/us/products/5146686>

Disposable pen, incl. adapter, integrated ink cartridge and pen station, writing thickness: 0.35 mm



UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>



CMS-INK-TR-C5 - Ink cartridge

5146684

<https://www.phoenixcontact.com/us/products/5146684>

Ink cartridge, special black ink, 5 cartridges of 1 ml each, for high demands



CMS-PEN 0,25 - Marker pen

5067815

<https://www.phoenixcontact.com/us/products/5067815>

Marker pen, incl. adapter, ink tank and reservoir, 0.25 mm nib



UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>



CMS-PEN 0,35 - Marker pen

5067828

<https://www.phoenixcontact.com/us/products/5067828>

Marker pen, incl. adapter, ink tank and reservoir, 0.35 mm nib



CMS-PEN 0,50 - Marker pen

5067831

<https://www.phoenixcontact.com/us/products/5067831>

Marker pen, incl. adapter, ink tank and reservoir, 0.5 mm nib



UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>



CMS-R-FLUID-TR - Cleaning fluid

5146750

<https://www.phoenixcontact.com/us/products/5146750>

Cleaning fluid, 30 ml, for the CMS-PEN ... and CMS-DISPOSABLE-PEN ...



CMS-R-FLUID-TR-C2 - Cleaning cartridge

5146752

<https://www.phoenixcontact.com/us/products/5146752>

Cleaning cartridges with replacement sealing caps, 2 cartridges with 10 ml cleaning fluid each and 2 caps for the CMS-PEN ... and CMS-DISPOSABLE-PEN ...



UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>



BM ID-MAG20 - Magazine

1044356

<https://www.phoenixcontact.com/us/products/1044356>



Infeed magazine for accommodating a max. of 20 UniCard sheets

BM ID-MAG40 - Magazine

1044357

<https://www.phoenixcontact.com/us/products/1044357>



Infeed magazine for accommodating a maxi. of 40 UniCard sheets

UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>



P1 UC-MAG 6 - Magazine

5146121

<https://www.phoenixcontact.com/us/products/5146121>



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating UC-EMP..., UC-EMLP...

CMS-R-SET-TR - Cleaning set

5146751

<https://www.phoenixcontact.com/us/products/5146751>



Cleaning set, consisting of: 1x cleaning cup, 2x cleaning cartridges with 10 ml cleaning fluid each and 2x replacement sealing caps for the CMS-PEN ... and CMS-DISPOSABLE-PEN ...

UC-EMLP (17X15) - Plastic label

0827885

<https://www.phoenixcontact.com/us/products/0827885>



BLUEMARK CLED - Printer

5147999

<https://www.phoenixcontact.com/us/products/5147999>

Printers with LED-UV technology for printing plastic labels in UniCard format.



Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com