
TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

APPLICATION TOOLING

HAND TOOLS



✔ Active

TE CONNECTIVITY (TE)

SAHT

AMP

1463405-1
TE Internal Number: 1463405-1

Out of Scope for EU RoHS
Out of Scope for EU ELV

Tool Grade Premium Crimp Tooling

Ratchet Configuration Not Releasable, Not Adjustable

Die Sets Type Fixed In Tool

Specification Type TE Product Specification (114-)

Calibration Certificate Yes

PRODUCT DRAWING
Japanese

DOCUMENTATION

Product Drawings

Straight Action Hand Tool

PDF **(TIFF AVAILABLE)**

Japanese

Product Specifications

Application Specification

CRIMPING OF MINI-MULTI-LOCK CONNECTOR CONTACTS

TIF

English

CRIMPING OF MINI-MULTI-LOCK CONNECTOR CONTACTS

PDF

English

Downloaded from Arrow.com.

Instruction Sheets

Instruction Sheet (non U.S.)

Straight Action Hand Tool For Mini Multi Lock Contact

PDF

English

Straight Action Hand Tool For Mini Multi Lock Contact

TIF

English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Other

Tool Grade Premium Crimp Tooling
Ratchet Configuration Not Releasable, Not Adjustable
Die Sets Type Fixed In Tool
Specification Type TE Product Specification (114-)
Calibration Certificate Yes
Power Type Manual
Tool Type Straight Action Hand Tool
Crimp Form-Wire Barrel Type Open Barrel - F Crimp

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance

PDF

Downloaded from Arrow.com.