



TP1410LF, Vinyl Locking Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [TP1410LF](#)



Vinyl Locking Fork Terminal For 16 - 14 AWG

Features

- Locking fork tongue design allows fast installation
- Screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

Application

For Fast Installation And Security

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards	UL486
Met	
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#16 AWG to #14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Locking Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
----------------	----------

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	26 mm
Dimension - Pad Width inch	0.36 in
Package Height	0.000 in
Dimension - Hole Size fraction	15/79
Dimension - Hole Size inch	0.19 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#10
Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Z inch	0.31 in
Dimension - Bolt Size fraction	#10
Cable Insulation Diameter	0.180 in
Maximum	
Dimension - Length Overall	1.02 in
inch	

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Sub Brand	VINYLUG
Color Code	Blue
Physical Attribute - Tongue	Locking Fork
Type	
Plated	Y
Feature - Barrel Style	Shrouded
Type	TP-LF, Locking
UPC 12 Digit	781810713754
UPC 14 Digit GTIN	00781810713754
Material	Copper
Plating Type	Tin
UPC	781810713754

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)

