


printed on 4 Nov 2024 13:46 (Eastern Standard Time) from TE354946



4. FLANGE SEAL IS INTENDED FOR NON-PRESSURIZED FLUID SPLASH ONLY, P/N: 1013-003-1206 SUPPLIED SEPARATELY.

3. MATERIAL:
SHELL: PA66 GF15 (BLACK)
WELD CAP: PA66 GF15 (BLACK)
GROMMET: VMQ (RED-ORANGE)
INSERTS: STAINLESS STEEL

2. THIS RECEPTACLE MATES WITH THE DT06-12SA-XXXX PLUG. (XXXX ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.

1. FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000 AND 0425-017-0000.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER E.O. P19337	03AUG06	-	RDR
	C	REVISED PER E.O. P20545	30SEP10	-	SB
	CI	REVISED PER PCN-24-225053	07OCT2024	RK	CB

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm ²] REF ONLY
16	.088 [2.24]	.145 [3.68]	14-20 AWG [2.5-0.5]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. YOHANNES	22JULY04	 TE Connectivity	
		CHK B. BYFORD	04AUG10		
		APVD S. BEARD	02AUG10	NAME 12 WAY RECEPTACLE-LE17 MOD. COLOR: BLACK DT SERIES	
		PRODUCT SPEC 108-151009			
		APPLICATION SPEC 114-151009		SIZE A3	CAGE CODE 00779
		WEIGHT 52.52 g		DRAWING NO C-DT04-12PA-LE17	RESTRICTED TO -
CUSTOMER DRAWING;		SCALE 1:1	SHEET 1	OF 1	REV CI