Part Number : 1300190004
Product Description : Die Block 2 Pole Shorting Plug with 0.610m (2.0') Chain, Yellow
Series Number : 130019
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 22804



Documents and Resources

Drawings

1300190004_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Connectors
Series	130019
Description	Die Block 2 Pole Shorting Plug with 0.610m (2.0') Chain, Yellow
IP Rating	N/A
Product Name	Die Block
Type	Die Block
UPC	78678822804

Agency

CSA	LR6837
UL	E46237

Electrical

Current - Maximum per Contact	25.0A
Voltage - Maximum	600V AC

Physical

Coupling Type	Push to Lock
Gender	Male
Keyway	None
Length	N/A
Material - Component	Nitrile/PVC
Mounting Thread Size	N/A
Net Weight	299.000/g
Orientation	N/A
Panel Mount	N/A
Poles	2

Downloaded from Arrow.com.

Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A

Downloaded from Arrow.com.