

Honeywell Sensing and Control

Search

2455 RC 86610001

(Home : Products : Sensors » Thermostats » 2455RC)



2455RC Series Ceramic Automatic Reset Thermostats

Actual product appearance may vary.

narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (5910)
- Switches (9781)
- Wireless (45)

Technology

- Electromechanical (9307)
- Magnetic (541)
- Microstructure (1495)
- Optical/Infrared (1042)
- Thick Film (1409)
- More...

new products**New Wireless Products**

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XTR6000™
find out more

white papers

- ▷ Wireless Switches Offer Unlimited Benefit
- ▷ Basic Switches Are Not Created Equal
- ▷ Applying Precision Switches
- ▷ Sensors for Medical Devices
- ▷ New Ways to Measure Torque
- ▷ Choosing Safety Switches
- ▷ Specifying Hour Meters

Need help?

Click here to contact us

[Sales & Service](#) [Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

| | |
|--------------------------------|--|
| Functional Properties | Close on rise |
| Reset Type | Automatic |
| Amperage | 15 A/10 A |
| Voltage | 120 Vac/250 Vac |
| Operating Temperature | 0 °C to 260 °C [32 °F to 500 °F] |
| Environmental Exposure Range | -20 °C to 287 °C [0 °F to 550 °F] |
| Open Temperature | 100.0 °C [212 °F] |
| Close Temperature | 48.9 °C [120 °F] |
| Open Tolerance | 2.8 °C [5 °F] |
| Close Tolerance | 4.4 °C [8 °F] |
| Dielectric Strength | MIL-STD-202, Method 301; 2000 Vac 60 Hz - Terminal to Case |
| Insulation Resistance | MIL-STD-202, Method 302; Cond. B - 500 MΩ 500 Vdc applied |
| Contact Resistance | MIL-STD-202, Method 307; 0.050 Ω |
| Housing Material | Ceramic |
| Contact Material | Silver/nickel alloy |
| Agency Approvals and Standards | UL, CSA, VDE |
| Mounting | B239 airstream bracket |
| Series Name | 2455RC |

contacts

- ▷ Customer Service
- ▷ Technical Support
- ▷ Global Sales & Service
- ▷ View Site Demo
- ▷ Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.

[Meet Dr. Larry](#)**my links**

- ▷ Login to iCOM
- ▷ Login to Rep/AD Portal
- ▷ Login to Digital University

News Center

- ▷ HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
- ▷ HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- ▷ HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION
- ▷ HONEYWELL INTRODUCES MICROPower OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

MICRO SWITCH

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)