Datasheet for part number MKJ3C7W12-37DN

Our Catalog Part Number: MKJ3C7W12-37DN
Our Global Manufacturing Part Number: 155404-1101
Brand: Cannon Product Category: Circular Product Line: Trinity MKJ Series: MKJ3

Product Datasheet	
Series	Bayonet Coupling
Class	Back- Potted Receptacle
Shell Style	Jam Nut Receptacle
Plating	Aluminum/OD Cad
Contact Arrangement	37 Contacts Size 23
Gender	Socket, PC Tail, 0.109 Extension
Polarization	Normal (150° 210°)
Contact Size / Spacing	#23 / 0.076 inches (1.9 mm)
Wire Acomodiation	#22 - #28 AWG
Current Rating	5 Amps Maximum
Voltage Rating	500 VAC RMS Sea Level
Insulator Resitance	5000 Megaohms Minimum
Operating Temperature	-55°/+150°
Contact Resistance	8 Milliohms Maximum
Vibration	20 g′ in Accordance with MIL-STD-1344 Method 2005, Condition IV
Shock	300 g′ (MKJ1) 50 g′ (MKJ0 and MKJ4) in Accordance with MIL-STD-1344 Method 2004, Condition E
EMI Shielding Effectiveness	40dB Attenuation, 100 MHz to 1000 MHz

Specifications and dimensions subject to change.

Downloaded from Arrow.com.