


OD5010 Series



DC Fans - 5, 12, 24V
50mm x 10.5mm (2.0" x 0.4")




Frame	PBT, UL94 V-0 Plastic	Operating Temperature -20°C ~ +65°C	
Impeller	PBT, UL94 V-0 Plastic	Storage Temperature -20°C ~ +75°C	
Connection	2x Lead Wires, 26 AWG	Life Expectancy 70,000 Hours (L10 at 40°C)	
Motor	Brushless DC, Auto Cutoff, Auto Restart, Electronically Protected, Polarity Protected	Available Options: Tachometer Output PWM Speed Control Input Alarm Output Sealed Sleeve Bearings IP Ratings	
Bearing System	Ball Bearings	Weight: 0.07 lbs.	
Dielectric Strength	500VDC/min, <1mA		
Insulation Resistance	≥10M Ohm @ 500 VDC		

Part Number	Rated Voltage (Volts DC)	Voltage Range (Volts DC)	Input Power (Watts)	Rated Current (Amps)	Rated Speed (RPM)	Max Airflow (CFM)	Noise Level (dBA)	Max Static Pressure ("H ₂ O)
OD5010-05HB	5	4.5 ~ 5.5	1.05	0.21	6490	12.7	35.1	0.18
OD5010-05MB	5	4.5 ~ 5.5	1.05	0.21	5475	10.8	33.2	0.14
OD5010-05LB	5	4.5 ~ 5.5	0.95	0.19	4425	8.6	25.4	0.09
OD5010-12HB	12	8 ~ 13.8	1.20	0.10	6490	12.7	35.1	0.18
OD5010-12MB	12	8 ~ 13.8	1.08	0.09	5475	10.8	33.2	0.14
OD5010-12LB	12	8 ~ 13.8	0.84	0.07	4425	8.6	25.4	0.09
OD5010-24HHB	24	20 ~ 26.4	2.40	0.10	7150	14.9	37.4	0.22
OD5010-24HB	24	20 ~ 26.4	1.92	0.08	6490	12.7	35.1	0.18
OD5010-24MB	24	20 ~ 26.4	1.68	0.07	5475	10.8	33.2	0.14
OD5010-24LB	24	20 ~ 26.4	1.44	0.06	4425	8.6	25.4	0.09

OD5010 Series with Alarm




DC Fans with Alarm - 12, 24V
50mm x 10.5mm (2.0" x 0.4")



Frame	PBT, UL94 V-0 Plastic	Operating Temperature -20°C ~ +65°C Storage Temperature -20°C ~ +75°C Life Expectancy 70,000 Hours (L10 at 40°C) Installed Options: Open Collector Alarm Output Available Options: Inverted Alarm State 5V TTL Type Alarm Output Weight: 0.07 lbs.	Static Pressure ("H₂O") vs. Airflow (CFM) graph showing performance curves for HH, H, M, and L models.
Impeller	PBT, UL94 V-0 Plastic		
Connection	3x Lead Wires, 24 AWG		
Motor	Brushless DC, Auto Cutoff, Auto Restart, Electronically Protected, Polarity Protected		
Bearing System	Ball Bearings		
Dielectric Strength	500VDC/min, <1mA		
Insulation Resistance	≥10M Ohm @ 500 VDC		

Part Number	Rated Voltage (Volts DC)	Voltage Range (Volts DC)	Input Power (Watts)	Rated Current (Amps)	Rated Speed (RPM)	Max Airflow (CFM)	Noise Level (dBA)	Max Static Pressure ("H ₂ O")
OD5010-12HB02A	12	8 ~ 13.8	1.20	0.10	6490	12.7	35.1	0.18
OD5010-12MB02A	12	8 ~ 13.8	1.08	0.09	5475	10.8	33.2	0.14
OD5010-24HB02A	24	20 ~ 26.4	1.92	0.08	6490	12.7	35.1	0.18
OD5010-24MB02A	24	20 ~ 26.4	1.68	0.07	5475	10.8	33.2	0.14



Alarm Max Pullup Voltage: Fan Vcc
Alarm Max Sink Current: 5mA