

Part Number : [190710155](#)


Product Description : InsulKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 5/16" (M8), Length 36.25mm, Mylar Tape Carrier

Series Number : 19071

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : D-651-56XT



Documents and Resources

Drawings

[190710155_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-19902-009-001.pdf](#)

[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19071
Description	InsulKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 5/16" (M8), Length 36.25mm, Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	InsulKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753071254

Agency

UL	E32244
----	--------

Electrical

Voltage - Maximum	300V
-------------------	------

Physical

Barrel Type	Closed - Brazed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	4.037/g
Packaging Type	Adhesive Tape on Reel
Stud Size	5/16" (M8)
Wire Insulation Diameter	9.78mm
Wire Size (AWG)	8
Wire Size mm ²	8.36

Application Tooling

This document was generated on Apr 29, 2026