

Micro USB to USB OTG Host Adapter Cable, Right-Angle 5-Pin USB Micro-B to A (M/F), 6-in. (15.24 cm)

MODEL NUMBER: U052-06N-RA



Connects a USB peripheral, such as a thumb drive or keyboard/mouse, to OTG-enabled smartphones, tablets and other devices. Ideal for sharing data and downloading video.

Features

Connects a USB-A Peripheral to Your OTG-Enabled Mobile Device

- Ideal for sharing data and downloading video
- Right-angled Micro-B connector for easy installation in tight spaces
- Allows connection of USB hub to connect more devices
- Plug and play—no software, drivers or external power supply

Premium Construction for Superior Signal Transfer

- Foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated contacts
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

Specifications

OVERVIEW	
UPC Code	037332196538
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	

Highlights

- Right-angled Micro-B connector for easy installation in tight spaces
- Plug and play—no software, drivers or external power supply
- Premium double shielding for error-free signal quality
- Molded nickel-plated connectors with gold-plated contacts
- Allows connection of USB hub to connect more devices

System Requirements

- OTG-enabled smartphone, tablet or other mobile device

Package Includes

- U052-06N-RA Micro USB to USB OTG Host Adapter Cable (M/F), 6 in.



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	MICRO-USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Angled
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	6.00 x 4.00 x 0.50
Shipping Dimensions (hwd / cm)	15.24 x 10.16 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85%, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.