



Part Number : [1301360036](#)
Product Description : Super-Safeway Multi-Tap (3)
NEMA 5-15 Outlet Box with Buss Bars, 7.62m (25.0')
Cord Length, 14/3 SOOW Cord, NEMA 5-15 Plug
Series Number : 130136
Status : Active
Product Category : Power Distribution
Engineering Number : 31593A143



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power Distribution
Series	130136
Description	Super-Safeway Multi-Tap (3) NEMA 5-15 Outlet Box with Buss Bars, 7.62m (25.0') Cord Length, 14/3 SOOW Cord, NEMA 5-15 Plug
Enclosure Rating	N/A
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Multi-Tap and Strip Cordset
UPC	78678879632

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	120V

Physical

Cord Diameter	13.59mm (.535")
Cord Grip Body Size	Double C-Clamp
Cord Length	7.62m (25.0')
Cord Type	14/3 SOOW
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber

Mounting Style	Portable
Net Weight	4101.400/g
Number of Receptacles	3
Packaging Type	Carton
Receptacle Type	Triple

This document was generated on Sep 16, 2025