



Part Number : [1300390382](#)
Product Description : Micro-Change Terminator, Male Standard with Resistor, 5 Pole
Series Number : 130039
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : DND100




Documents & Resources

Drawings
[1300390382_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130039
Description	Micro-Change Terminator, Male Standard with Resistor, 5 Pole
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Terminator
UPC	78172553456

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	Polyamide
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	98.000/g
Orientation	Straight
Poles	5
Temperature Range - Operating	0°C to +60°C

Wire Size (AWG)	N/A
-----------------	-----

This document was generated on Apr 16, 2025