

Cat6a Pass-Through Cassette - (x12) RJ45

MODEL NUMBER: **N484-12RJ**



Highlights

- High Density Copper Cassette for use with the N484-00U and N484-01U chassis'
- Cat6a Pass-through Cassette, with (x12) RJ45 connections
- Rated for 10 Gbps Ethernet data transfer speeds

Package Includes

- N484-12RJ Cat6a Pass-Through Cassette - (x12) RJ45
- Quick Start Guide

Description

Tripp Lite's N484-12RJ is a High Density Cat6a Pass-through Cassette with (x12) RJ45 connections. Designed specifically for use with Tripp Lite's N484-00U and N484-01U chassis'; up to 4 cassettes per N484-01U, or 1 per N484-00U. Each RJ45 connection is rated for 10 Gbps Ethernet data transfer speeds. Installation is simple, with the cassette being easily installed or removed using screw tabs to lock or unlock it from the panel; no tools required. Furthermore, each cassette features factory terminated connectors that reduce the time and labor required of field connector terminations. Cassette housing is manufactured with heavy duty, 1.0mm Cold Rolled Steel.

Features

- High Density Copper Cassette for use with the N484-00U and N484-01U chassis'
- Cat6a Pass-through Cassette, with (x12) RJ45 connections
- Rated for 10 Gbps Ethernet data transfer speeds
- Installation is simple, with the cassette being easily installed or removed using screw tabs to lock or unlock it from the panel; no tools required
- Each cassette features factory terminated connectors that reduce the time and labor required of field connector terminations.
- Housing made of heavy duty, 1.0mm Cold Rolled Steel

Specifications

OVERVIEW	
UPC Code	037332187222
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	5.99 x 20.07 x 3.71
Shipping Dimensions (hwd / in.)	2.36 x 7.90 x 1.46
Shipping Weight (kg)	0.23
Shipping Weight (lbs.)	0.51
ENVIRONMENTAL	
Operating Temperature Range	-4 to 122 F (-20 to 50 C)
CONNECTIONS	
Ports	12
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	Cat6a
CERTIFICATIONS	
Approvals	RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>