
696722-1 Product Details



696722-1

TE Internal Number: 696722-1

Active

Ring and Spade Tongue Terminals

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Terminal Shape = Ring Tongue
- Receptacle Style = Flag
- Body Style = STRATO-THERM
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

[+] Feedback

Documentation & Additional Information

Product Drawings:
- None Available

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Receptacle Style = Flag
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire
- Insulation = No
- Insulation Support = Non-Insulation Support
- Stud Size = 8 [M4]
- Shape = RING-089
- Heavy Duty = No
- Finish = Nickel

Termination Features:
- Wire/Cable Size (CMA) = 13,100 – 20,800

Dimensions:
- Stud Diameter (mm [in]) = 4.34 [0.171]

Body Features:
- Body Style = STRATO-THERM
- Wire Range (mm [AWG]) = 8.00² [8]
- Material = Copper

Contact Features:
- Terminal Shape = Ring Tongue

Industry Standards:
- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Features:
- Packaging Method = Loose Piece

Other:
- Brand = AMP

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

Downloaded from Arrow.com.