



| SIGN | DATE | DESCRIPTION | APPROVER |
|---|---|---|---|
| ⚠1 | 11/21'09 | The normal grey No. changed from RAL7004/P to RAL7035/D | Kind |
| ⚠2 | 04/06'10 | Add the 2P mark & Wire strip length is changed | RUNNER |

*THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!*




SECTION A-A

## Material

- Item 1 Terminal top body:Thermoplastic ( UL94V-0 )
- Item 2 Terminal down body:Thermoplastic ( UL94V-0 )
- Item 3 Terminal lever:Thermoplastic ( UL94V-0 )
- Item 4 Wire guard:Stainless Steel
- Ltem 5 Female contact:PhBz ( CuSn ) Tin plated

## Electrical cULus

- Voltage rating:300V
- Current rating:10A
- Solid wire(AWG):12-26
- Stranded wire(AWG):12-26
- ⚠4 Wire strip length:8-9mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C

HW xx 7 0 x 0 xxxx G

| | | | | |
|---|---|---|---|---|
| 02 | 2 CONTACTS | 0 Black | 0000 Standard @ Logo | RoHS |
| 03 | 3 CONTACTS | 5 Green (RAL 6018/T) | 000A Standard ANY Logo | Pb<40,000ppm |
| ... | ... | 6 Blue | Any special item by customer request, please contact sales department. | |
| 24 | 24 CONTACTS | ⚠8 Grey (RAL 7035/D) | | |

| Poles | 02 | 03 | 04 | 05 | 06 | 07 | 08 | 09 | 10 | 11 | 12 | 13 |
|---|---|---|---|---|---|---|---|---|---|---|---|---|
| Dim L | 10.10 | 15.10 | 20.10 | 25.10 | 30.10 | 35.10 | 40.10 | 45.10 | 50.10 | 55.10 | 60.10 | 65.10 |
| Dim B | 5.00 | 10.00 | 15.00 | 20.00 | 25.00 | 30.00 | 35.00 | 40.00 | 45.00 | 50.00 | 55.00 | 60.00 |
| TOL | ±0.15 | | | | | ±0.20 | | | | | | ±0.25 |
| Poles | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 23 | 24 | |
| Dim L | 70.10 | 75.10 | 80.10 | 85.10 | 90.10 | 95.10 | 100.10 | 105.10 | 110.10 | 115.10 | 120.10 | |
| Dim B | 65.00 | 70.00 | 75.00 | 80.00 | 85.00 | 90.00 | 95.00 | 100.0 | 105.0 | 110.0 | 115.0 | |
| TOL | ±0.25 | | | | | ±0.30 | | | | | | |

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

| | | | | | |
|---|---|---|---|---|---|
| TITLE | HW 5.0 Series ( W/O ) contact on down side | | | | |
| PART NO. | HWxx70x0xxxxG | | | DWG NO. | 8HW0802 |
| APPROVED | CHECKED | DESIGNED | DRAWN | CUST NO. | |
| | | Runner 2010.04.06 | Runner 2010.04.06 | UNIT: mm<br>SCALE: NONE<br>SHEET: 01/01<br>REV.: D | |

| Tolerance | |
|---|---|
| X. | ±0.50 |
| X.X | ±0.30 |
| X.XX | ±0.10 |
| X° | ±1° |

Downloaded from Arrow.com.