



Part Number : [1210010099](#)

Product Description : mPm DIN Adapter, Form B-11mm, Internal Threads, 2 Poles with C4 Circuit, 115V, Yellow LED, A03 Series Light Adapter

Series Number : 121001

Status : Obsolete

Product Category : Circular Industrial Connectors

Engineering Number : A03C4L



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/108/2014 (17 Dec 2014)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Obsolete
Category	Circular Industrial Connectors
Series	121001
Description	mPm DIN Adapter, Form B-11mm, Internal Threads, 2 Poles with C4 Circuit, 115V, Yellow LED, A03 Series Light Adapter
IP Rating	IP65, IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	883906500542

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	115V

Physical

Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Form	B - 11mm
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	999.990/g
Orientation	90° Angle
Pitch - Mating Interface	11.00mm

Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size (AWG)	N/A

This document was generated on Oct 11, 2025

Obsolete