

USB 3.0 SuperSpeed to 2.5 in. SATA III Encrypted Hard Drive Enclosure with Keypad Lock and UASP Support

MODEL NUMBER: U357-025-SEC



Password-protected enclosure connects a 2.5 in. SATA hard disk drive or solid state drive to your computer's USB 3.0 port for extra storage and fast data transfer. UASP-enabled for 70% more speed with UASP host controller.

Description

The U357-025-SEC USB 3.0 SuperSpeed to 2.5 in. SATA Encrypted Hard Drive Enclosure is a quick, easy way to connect a SATA HDD (Hard Disk Drive) or SSD (Solid State Drive) to your laptop, netbook or notebook's USB 3.0 port.

In addition, it provides state-of-the-art real-time 256-bit AES encryption to ensure all data stored on the SATA drive is for your eyes only. A secure keypad lock provides password security for secret documents and files. If the enclosure is lost or stolen, your data remains protected. Change your custom password as often as you like.

Perfect for portable storage or backing up sensitive data, the compact enclosure is compatible with 2.5-inch SATA drives up to 2 TB (and will support larger drives when available). It supports USB 3.0 data transfer rates up to 5 Gbps. It also reads data up to 70 percent faster and writes up to 40 percent faster than USB 3.0 when connected to a UASP-enabled host controller.

The U357-025-SEC accepts SATA III, II and I drives and is backward-compatible with previous USB generations. No software, drivers or external power supply is required. Compatible with any USB-enabled operating system.

Features

Quickly Connects a SATA Drive to Your Computer's USB 3.0 Port

- Recommended for portable storage or backing up sensitive data
- Supports USB 3.0 data transfer rates up to 5 Gbps

Highlights

- Keypad lock provides password security for important files
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Works up to 70% faster when connected to UASP host controller
- Compatible with 2.5 in. SATA HDDs and SSDs up to 2 TB
- Recommended for 256-bit AES-encrypted portable storage

System Requirements

- 2.5 in. SATA HDD or SSD with 9.5 mm maximum height
- Device with USB port (USB 3.0 required to achieve USB 3.0 speeds)
- USB-enabled operating system
- UASP-enabled host controller required for UASP performance

Package Includes

- U357-025-SEC USB 3.0 SuperSpeed to 2.5 in. SATA Encrypted Hard Drive Enclosure
- USB 3.0 A to Micro-B device cable, 2 ft.
- Owner's manual



Powering Business Worldwide



- Features UASP for performance up to 70% faster when connected to UASP-enabled host controller
- Compatible with any USB-enabled operating system

State-of-the-Art Security Protects Your Data

- Real-time 256-bit AES encryption protects data from unauthorized access
- Secure keypad lock provides password security for sensitive documents and files
- Custom password can be changed as often as you like

Compatible with 2.5 in. SATA Drives Up to 2 TB

- Accepts SATA III, II and I drives
- Backward compatible with previous USB generations
- Works with both SATA HDDs and SSDs

Built for Portable Use

- Plug and play—no software, drivers or external power supply needed
- Portable tool-free design for quick on-the-move external storage
- SATA drive slides easily into convenient tray
- Protective cover keeps dust and dirt away from sensitive SATA drives
- USB 3.0 Micro-B device cable included

Specifications

OVERVIEW	
UPC Code	037332200907
Drives Supported	2.5" HDD and SSD
Technology	SATA/eSATA
INPUT	
Bus Powered	Yes
POWER	
Power Consumption (Watts)	5
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Read, Write, Power); Orange (PIN setting); Red (Lock); Blue (Unlock)



Powering Business Worldwide



PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	1.80 x 5.00 x 7.10
Shipping Dimensions (hwd / cm)	4.57 x 12.70 x 18.03
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	1.8 x 12 x 7.8
Unit Packaging Type	Box
Unit Weight (lbs.)	0.2
Unit Weight (kg)	0.09
ENVIRONMENTAL	
Operating Temperature Range	50 to 122 F (10 to 50 C)
Storage Temperature Range	32 to 149 F (0 to 65 C)
Relative Humidity	10% to 80% RH, Non-Condensing
BTUs	17.1 BTU/Hr
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
UASP Support	Yes
Driver Required	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.