




C2G

Discontinued - 29.5ft (9m) SC-SC 50/125 OM2 Duplex Multimode Fiber Optic Cable - Low Smoke Zero Halogen LSZH - Orange
Part No. 36329



Cost-effective solution that provides higher bandwidth and transmission rates and supports longer distances with lower loss than 62.5/125 fiber. Specifically designed for use with today's narrower aperture components, this cable is fully compatible with multimode applications. The LSZH jacket is composed from materials that lessen the smoke and halogen emissions when the cable is exposed to extreme temperatures.

This reduces the amount of harmful toxic and corrosive gases that cabling made with plastic materials would otherwise emit into the air during combustion. This construction makes LSZH cables ideal for use where the protection of people and equipment from harmful corrosive gases is absolutely critical.

The patented injection molding process provides each connection greater durability in resisting pulls, strains and impacts from cabling installs.

Each cable is 100% optically inspected and tested for insertion loss before you receive it. A pull-proof jacket design surrounds the popular 50/125 multimode fiber, immune to electrical interference.

Features & Benefits

Designed to support gigabit ethernet, fibre channel, ATM, or any application that requires high speed data transfer

Low Smoke Zero Halogen (LSZH) jacket lessen harmful smoke and halogen emissions when the cable is exposed to extreme temperatures

Patented injection molding process for greater durability

Optically inspected and tested for insertion loss

Pull-proof jacket design, immune to electrical interference

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|-----------|
| Product Line | C2G | Color | Orange |
| UPC Number | 757120363293 | Country Of Origin | Hong Kong |
| Application Sector | Commercial, Industrial | Type | Cable |

Dimensions

| | | | |
|-------------------|---------|--------------|---------|
| Product Length US | 29.5 FT | Cable Length | 29.5 ft |
|-------------------|---------|--------------|---------|

Technical Information

| | | | |
|------------------------|-----------------------|-----------------|-------------|
| Fiber Optic Cable Type | Multimode, OM2 | Jacket Material | LSZH PVC |
| Jacket Application | Riser Rated | Bend Radius | 50 mm |
| Simplex/Duplex | Duplex | Cable Type | Fiber Optic |
| Jacket Rating | FT4 Rated, OFNR Rated | Connector 2 | SC Male |
| Connector 1 | SC Male | Fiber Size | 50/125 |