



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		A	NEW DRAWING PER ECO-14-014953	07OCT2014	NK	RH

CONVERSION CHART

INCH	MM
.010	0.25
.024	0.60
.030	0.75
.039	1.00
.045	1.14
.078	2.00
.100	2.54
.115	2.92
.160	4.06
.169	4.30
.200	5.08
.270	6.85
.276	7.00
.315	8.00
.394	10.00
.500	12.70
.780	19.81
1.142	29.00
1.201	30.50
1.299	33.00



1 DPS9SG902 DOES NOT HAVE SOLDER PINS.

SPECIFICATIONS:

- CONTACT RATING: 0.4VA @ 20 VDC OR PEAK AC.
- CONTACT RESISTANCE: 100 MILLIOHMS MAX.
- MECHANICAL LIFE: MORE THAN 10⁶ OPERATIONS.
- OPERATING TEMPERATURE: -10°C TO +60°C.
- CHARACTER HEIGHT/COLR: 4.30 mm[.169 in] WHITE ON BLACK BACKGROUND.

DIAL POSITION	DIAL MARKING *				
	NO LETTER	C	D	E	F
0	0	(STOP)	(STOP)	0	(STOP)
1	1	1	1	1	1
2	2	2	2	2	2
3	3	3	3	3	3
4	4	4	4	4	4
5	5	5	5	5	5
6	6	6	6	6	6
7	7	(STOP)	7	7	7
8	8		8	8	8
9	9		9	9	9
10	10		10	△	10
11	11		11	X	11
12	12		12	(STOP)	(STOP)
13	13		13		
14	14		14		
15	15		15	(STOP)	

HEXIDECIMAL CODE					
DIAL POSITION	C	1	2	4	8
0	X				
1	X	X			
2	X		X		
3	X	X	X		
4	X			X	
5	X	X		X	
6	X		X	X	
7	X	X	X	X	
8	X				X
9	X	X			X
10	X		X		X
11	X	X	X		X
12	X			X	X
13	X	X		X	X
14	X		X	X	X
15	X	X	X	X	X

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.25[.010]
4 PLC ± -
ANGLES ± 1°
FINISH -

DWN 07OCT2014
NAGALAKSHMI K

CHK 07OCT2014
HILL RYAN

APVD 07OCT2014
HILL RYAN

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
CODE SWITCH,
PUSHWHEEL DPS9SG902

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=4-1437603-7

RESTRICTED TO
-

SCALE
2:1

SHEET
1 of 1

REV
A