

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5033081810

Status:

Active

Overview:

SlimStack™ 0.40mm Pitch Board-to-Board Connectors

Description:

0.40mm Pitch SlimStack Board-to-Board, Plug, Surface Mount, Dual Row, Vertical Stacking, 0.70mm Stacking Height, 18 Circuits

Documents:

3D Model

Drawing (PDF)


Product Specification PS-503304-001-001 (PDF)

Application Specification AS-503304-001-001 (PDF)

Packaging Specification SPK-503308-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	503308
Application	Board-to-Board, Signal
Overview	SlimStack™ 0.40mm Pitch Board-to-Board Connectors
Product Name	SlimStack
UPC	884982169432
Physical	
Breakaway	No
Circuits (Loaded)	18
Circuits (maximum)	18
Color - Resin	Black
Durability (mating cycles max)	30
Glow-Wire Capable	No
Mated Height	0.70mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	7.832/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.40mm
Polarized to Mating Part	No
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	0.3A
Voltage - Maximum	50V AC/DC
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-503304-001-001
Packaging Specification	SPK-503308-001-001
Product Specification	PS-503304-001-001
Sales Drawing	SD-503308-001, SD-503308-002



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

503308 Series

Mates With

SlimStack Board-to-Board Receptacle 503304 , 503489

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION