



**Part Number :** 1301270003  
**Product Description :** Super-Safeway Three Wire and GFCI Circuit Tester, 3 Indicating Lights, Push to Test Button  
**Series Number :** 130127  
**Status :** Active  
**Product Category :** Wiring Devices  
**Engineering Number :** 1751



---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

## General

Status	Active
Category	Wiring Devices
Series	130127
Description	Super-Safeway Three Wire and GFCI Circuit Tester, 3 Indicating Lights, Push to Test Button
IP Rating	N/A
NEMA Configuration	N/A
Product Family	Testers
Product Name	Super-Safeway
Specialty	Testing
Type	Tool Ground Continuity Tester
UPC	78678875301

## Agency

UL	E38751
----	--------

## Electrical

Current - Maximum per Contact	N/A
GFCI	Yes
Voltage - Maximum	115V

## Physical

Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Lighted Connector	No
Locking Blade	N/A
Net Weight	211.000/g
Poles	N/A
Receptacle Type	GFCI Single

---

---

This document was generated on Sep 11, 2023