

Color: silver-colored

Material data	
Color	silver-colored
Fire load	0 MJ
Weight	9.2 g

Commercial data	
PU (SPU)	20 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454229733
Customs tariff number	7407100000

Product classification	
UNSPSC	39121613
eCl@ss 10.0	27-14-11-39
eCl@ss 9.0	27-14-11-39
ETIM 9.0	EC001522
ETIM 8.0	EC001522
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption



Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 790-133

↓

Documentation

Bid Text			
790-133	19.02.2019	xml 2.54 KB	↓
790-133	31.08.2017	doc 23.00 KB	↓

CAD/CAE-Data


CAD data	CAE data
2D/3D Models 790-133	EPLAN Data Portal 790-133
↓	↓
	WSCAD Universe 790-133
	↓

1 Compatible Products


1.1 Optional Accessories

1.1.1 Shield termination

1.1.1.1 Shield clamping saddles




Item No.: 790-108
Shield clamping saddle; 11 mm wide; diameter of compatible conductor; 3 ... 8 mm



Item No.: 790-208
Shield clamping saddle; 12.4 mm wide; 3 ... 8 mm



Item No.: 790-116
Shield clamping saddle; 19 mm wide; diameter of compatible conductor; 7 ... 16 mm




Item No.: 790-216
Shield clamping saddle; 21.8 mm wide; 6 ... 16 mm



Item No.: 790-124
Shield clamping saddle; 27 mm wide; diameter of compatible conductor; 6 ... 24 mm



Item No.: 790-220
Shield clamping saddle; 30 mm wide; 6 ... 20 mm




Item No.: 790-140
Shield clamping saddle; diameter of compatible conductor

1.1.1.2 Shield termination




Item No.: 791-107
Shield clamp; diameter of compatible conductor; 1.5 mm to 6.5 mm; H max. 40 mm; 10 mm wide



Item No.: 791-117
Shield clamp; diameter of compatible conductor; 10 mm to 17 mm; H max. 63 mm; 23 mm wide



Item No.: 791-124
Shield clamp; diameter of compatible conductor; 16 mm to 24 mm; H max. 78 mm; 30 mm wide



Item No.: 791-111
Shield clamp; diameter of compatible conductor; 5 mm to 11 mm; H max. 47 mm; 17 mm wide

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com