

Eaton BSPMA3480DLGR

Catalog Number: BSPMA3480DLGR

Eaton Bussmann series BSPM series surge arrester, Technology type MOV, 230/400 Wye (4W+G), Surge arrester, Thermoplastic, UL94V1, 50/60 Hz, 200 Kilo Ampere, Thermoplastic, Remote Contact

General specifications



Product Name

Eaton Bussmann series BSPM series surge arrester

Catalog Number

BSPMA3480DLGR

UPC

051712709088

Product Length/Depth

2.13 in

Product Height

3.54 in

Product Width

2.56 in

Product Weight

0.73 lb

Warranty

Five year limited warranty

Compliances

Contact factory
RoHS Compliant

Certifications

UL 94V0
UL Listed

Type

Surge arrestor

Special features

Technology type MOV

Application

Surge Protection

Frequency rating

50/60 Hz

Nominal Discharge Current

20 kA

Operating voltage

385

Voltage rating

230/400 Wye (4W+G)

Enclosure

Thermoplastic, UL94V1

Surge current

200 kA

Indicator type

Remote contact

Short-circuit rating

200 kA

Operating temperature

-35 to 85 °C

Mounting Method

35 mm DIN rail

Degree of protection

IP20

Material

Thermoplastic

Catalogs

[BSPMA3480DLGR~480V Delta, 3P](#)

[Bussmann series complete full line catalog no. 1007](#)

Specifications and datasheets

[Eaton Specification Sheet - BSPMA3480DLGR](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia