

Han HPR SP1-PFT/TE-SCL-M40



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 40 011 1113 |
| Specification | Han HPR SP1-PFT/TE-SCL-M40 |
| HARTING eCatalogue | https://harting.com/19400111113 |

Identification

| | |
|--------------------------|----------------------------|
| Category | Hoods / Housings |
| Series of hoods/housings | Han® HPR |
| Type of hood/housing | Panel feed through housing |

Version

| | |
|-------------------------|---|
| Size | SP1 |
| Version | Top entry |
| Number of cable entries | 1 |
| Cable entry | 1x M40 |
| Locking type | Screw locking |
| Field of application | Hoods/housings for harsh outdoor environments |

Technical characteristics

| | |
|--|--|
| Tightening torque | 6 Nm Locking screw |
| | 6 Nm Fixing screws |
| | 10 Nm Retaining ring |
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65 |
| | IP68 |
| | IP69 / IPX9K acc. to ISO 20653 |
| Type rating acc. to UL 50 / UL 50E | 4 |
| | 4X |
| | 12 |



Pushing Performance
Since 1945

Technical characteristics

Thickness of the panel ≥ 2 mm

Material properties

| | |
|-------------------------|---|
| Material (hood/housing) | Aluminium die-cast Corrosion resistant |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (seal) | NBR |

Specifications and approvals

| | |
|-----------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE DNV GL |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 254 g |
| Country of origin | China |
| European customs tariff number | 85389099 |
| GTIN | 5713140831681 |
| eCl@ss | 27440202 Shell for industrial connectors |
| ETIM | EC000437 |
| UNSPSC 24.0 | 39121466 |