



## T 3361 001 U

### Description

Female cable connector 5 pole IP40; solder; silver; straight; screw

**RATED\_CURRENT**

5 (A)


**RATED\_VOLTAGE**

300 (V)

**NUMBER\_OF\_POSITIONS**

5

**PROTECTION\_CLASS\_MATED** IP40



add to cart

add to favorite

send request

Technical data

Downloads

### General Characteristics

<b>CONTACT_DIAMETER_1</b>	1,5 mm
<b>CONTACT_TERMINATION_1</b>	SOLDER PIN
<b>GENDER</b>	FEMALE
<b>MAX_CABLE_DIAMETER</b>	(MM) 6
<b>MIN_CABLE_DIAMETER</b>	(MM) 4
<b>NUMBER_OF_POSITIONS</b>	5
<b>PART_CATEGORY</b>	FEMALE CABLE CONNECTOR
<b>PROTECTION_CLASS_MATED</b>	IP40

### Further Characteristics

<b>CONTACT_WIRE_GAUGE_MAX_1</b>	0.5
<b>CONTACT_WIRE_GAUGE_MIN_1</b>	0.05
<b>ZROHS01</b>	X

### Electrical Characteristics

<b>RATED_CURRENT</b>	(A) 5
<b>RATED_VOLTAGE</b>	(V) 300

find out more information about our new products.  
[Read more](#)

download our product catalogues and additional information.  
[Read more](#)

Amphenol Corporation. With more than 70 000 employees the organisation belongs to the leading manufacturers of electrical, electronic and fiber optic connectors worldwide. [Read more](#)

[Contact](#)

[Career](#)

[Downloads](#)

[Terms of use](#)

[Data protection](#)

[General Conditions](#)