

Cable tie tool for 4.6 - 13.5mm, manual, 0.369kg, blue

Art.-No. 110-88002 | EVO9iSP-MET/PL-BU | [Details](#)



- Cuts ties from 50 to 250 lb with a clean, flush cut for personnel safety and wire insulation integrity.
- Quality construction with impact-resistant housing, tested at over 1 million cycles, provides high durability resulting in fewer repairs and an extended product life.
- Lightweight tool with the most technologically advanced ergonomic design for reducing work-related risks such as fatigue and injury that affect productivity.
- Industrial EVOi provides calibrated tensioning with operational reliability in securing bundles.
- Tension dial offers 33 precise, easy-to-read settings (with ¼" increments) that reduce subjectivity or the need for fine tuning.
-



More products in this product group:

[Manual tensioning tool plastic housing >](#)

Application HellermannTyton's EVO 9i industrial-grade, mechanical hand tool is ergonomically designed to reduce the risks of repetitive stress injuries to operators while simultaneously increasing productivity. The EVO 9i Tension/Lock/Cut Technology delivers performance, safety and comfort for operators. Calibrated tensioning assures consistent wire-bundle tension before flush cut-off. Available in a standard grip span (EVO 9i) or short grip span (EVO 9iSP) for smaller hands. Additional accessories are available.

Colour	Blue (BU)
Description	EVO9iSP
For Cable Tie Width	0.18 - 0.53 "
For Cable Tie Width	4.6 - 13.5 mm
For Ties	T50, T80, T120, T150, T250, T255, WS, LK2, LK3, LK5, GL, ECO Series
Material	Metal (MET), Plastic (PL)
Operation	manual
PART DESCRIPTION	EVO9iSP-MET/PL-BU
Pack Cont.	1 pc.
Package Content packed in	box
Product Family	EVO9iSP up to 13.5 mm strap width
Product Group	Manual tensioning tool plastic housing
Strap Thickness max.	2.0 mm
Tool property	Manual clipping
Tool suitable cable tie material	Plastic
Type	EVO9iSP

Product Dimensions

Strap Width max.	13.5 mm
Tension Setting	Adjustable
Weight/Unit	0.369 kg

CE Certification	NO
CSA Certified	No
ELV compliant (Article 4 - 2)	YES
Hazardous Goods	No
ROHS compliant	Yes
Specifications	RoHS ✓
UL Listed (US and Canada)	No
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No
UL Recognized (US and Canada)	No

Logistics and Packaging

Country of Origin	CN
Customs Number	82055980
GTIN-13 / EAN	4031026621838
Packaging 1 - Height (m)	0.055 m
Packaging 1 - Length (m)	0.187 m
Packaging 1 - Qty	1
Packaging 1 - Type	carton
Packaging 1 - Volume (m³)	0.00242 m³
Packaging 1 - Weight (kg)	0.619 kg
Packaging 1 - Width (m)	0.235 m
Packaging 4 - Length (m)	1.2 m
Packaging 4 - Type	pallet
Packaging 4 - Width (m)	0.8 m

More Information

ETIM 7.0 Key	EC000453
ETIM 8.0 Key	EC000453
ETIM 9.0 Key	EC000453
UNSPSC Key	27112410

