



1 2 3 4 5 6

A

Minimum cable  $\phi$ :  $\phi F_{min}=3,0$ Maximum cable  $\phi$ :

- with rubber bushing :  $\phi F_{max}=9,0$
- without rubber bushing :  $\phi F_{max}=12,0$

09670370334	4-40UNC
Part number	screw thread

 <b>HARTING</b> All rights reserved Department EC PD - FR	All Dimensions in mm Original Size DIN A4			Scale 1:1 Free size tol.  Date 2013-01-29 State Final Release	Ref.  Sub.
	Created by DOUGE	Inspected by BAGDIKIAN	Standardisation KOHLER		
Title D-Sub Hood 37P side entry full metal			Doc-Key / ECM-Nr. 100521761/UGD/001/A 500000056836		
Type TB	Number 09670370334			Rev. A	Page 1/1