

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Mini
- Micro
- Accessory
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



P-555555-FFFFFM-S001

Operating Temperature: -20°C ~ +85°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: PVC

Certificate: NMEA 2000

You must login first for view the price

Quantity

- 1 +

Check Stock

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

M Series....

CAP-WBDM SMA1

-40°C ~ +105°C

- 0 +

NMEA 2000....

CAP-WMNF SMA1

-40°C ~ +105°C

- 0 +

NMEA 2000....

CAP-WMNF SMA1

-40°C ~ +105°C

- 0 +

NMEA 2000, Micro..

HMC-000505-...

-20°C ~ +80°C

- 0 +

NMEA 2000, Micro..

HMC-000505-...

-20°C ~ +80°C

- 0 +

NMEA 2000, Micro..

HMC-000505-...

-20°C ~ +80°C

- 0 +

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 4A	Connector Type Multi-Port T Adaptor
Shielded Plastic, Non-shielded	No. of Contacts 05
Connector Gender N/A	Backshell N/A
Mating Style Screw Thread	IP Rating IP68
Assembly Style N/A	
More Options	

People Also Bought

P-555555-FFFFFM-...

DC-03RFMS-RS8010

BD-068MMA-QL8A00

YA-A03M-A03F-...

MN-04AFFM-SL8004

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

Downloaded from [Arrow.com](#)