

Specification Sheet

Part Number: 156-00538



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

2-Piece Cable Tie with Edge Clip, 8.0" Long, EC4B, 1 - 3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg

Article Number 156-00538

Type T50REC4B

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Short Description 2-Piece Cable Tie with Edge Clip, 8.0" Long, EC4B, 1 - 3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg

Global Part Name T50REC4B-PA66HS/PA66HIRHS-BK

| | |
|-------------------------------------|-----------------|
| Minimum Tensile Strength (Imperial) | 50 |
| Minimum Tensile Strength (Metric) | 225 |
| Length L (Imperial) | 8.0 |
| Length L (Metric) | 202.0 |
| Fixation Method | Edge Clip |
| Identification Plate Position | none |
| Releasable Closure | No |
| Variant | Inside Serrated |
| Width W (Imperial) | 0.18 |
| Width W (Metric) | 4.6 |
| Bundle Diameter Min (Imperial) | 0.16 |
| Bundle Diameter Min (Metric) | 4.0 |
| Bundle Diameter Max (Imperial) | 1.77 |
| Bundle Diameter Max (Metric) | 45.0 |
| Thickness T (Imperial) | 0.05 |
| Thickness T (Metric) | 1.2 |

| | |
|--------------------------------|---|
| Height H (Imperial) | 0.63 |
| Height H (Metric) | 16.0 |
| Panel Thickness Min (Imperial) | 0.04 |
| Panel Thickness Max (Imperial) | 0.12 |
| Panel Thickness Min (Metric) | 1.0 |
| Panel Thickness Max (Metric) | 3.0 |
| Material | Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| Foot Part Material | PA66HIRHSUV |
| Material Shortcut | PA66HS PA66HIRHS |
| Material Cable Tie | Polyamide 6.6 heat stabilized (PA66HS) |
| Flammability | UL 94 HB |
| UV Resistant (Yes/No) | No |
| Use Conditions | For Indoor and Outdoor Use |
| Operating Temperature | -40°F to +230°F (-40°C to +110°C) -40°F to +221°F (-40°C to +105°C) |
| Reach Compliant (Article 33) | Yes |

| | |
|-----------------------------|------------|
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 500 |
| Package Quantity (Metric) | 500 |
| Customs Number | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)