







B



PIN NUMBER DETAIL

2




P.C.B. RECOMMENDED HOLE LAYOUT
SEEN FROM COMPONENT SIDE

ALL CENTERLINE DIMENSIONS ARE BASIC.

NOTES:

- CONNECTOR MATERIALS:
HOUSING: THERMOPLASTIC UL94 V-0
CONTACTS/SHIELD: COPPER ALLOY
SHIELD PLATING: NICKEL
RJ45 CONTACT PLATING: SELECTIVE GOLD OR EQUIVALENT IN THE CONTACT AREA SEE CHART FOR PART NUMBER
USB CONTACT PLATING: PER USB SPEC 2.0
- FOR PRODUCT SPECIFICATIONS SEE PR022-01.
- DIMENSIONS AND TOLERANCES COMPLY WITH TIA-1096 STANDARD.
- △ PART NUMBER AND DATE CODE MARKED APPROXIMATELY AS SHOWN.

50 MICRO-INCHES [1.27um]	SS-76800-006
CONTACT PLATING IN MATING AREA	PART NUMBER




DO NOT SCALE DRAWING
DRAWING IS SUBJECT TO
CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE ±.005 [0.13]
ANGLES ARE ± 1°

SHEET NO. 1 OF 1



stewart
CONNECTOR
a bel group

11118 Susquehanna Trail South
Glen Rock, PA 17327-9199
(717) 235-7512
<http://www.stewartconnector.com>

TITLE: PASSIVE COMBO JACK, TAB UP RJ45 AND DUAL USB "A" SHIELDED, NF			
DRN BY:	TRM	DATE	3-25-09
APPD BY:	DHG	DATE	3-25-09
DWG NO.	CT760011	REV.	A7

RoHS



1

AutoCAD

B

A