

Eaton BSPMA2240S3GR

Catalog Number: BSPMA2240S3GR

Eaton Bussmann series BSPM series surge arrester, Technology type MOV, 230/400 Wye (4W+G), Surge arrester, Thermoplastic, UL94V14, 50/60 Hz, 200 Kilo Ampere, Thermoplastic, Remote Contact



General specifications

Product Name

Eaton Bussmann series BSPM series surge arrester

Catalog Number

BSPMA2240S3GR

UPC

051712709040

Product Length/Depth

1.42 in

Product Height

3.54 in

Product Width

2.56 in

Product Weight

0.52 lb

Warranty

Five year limited warranty

Compliances

Contact factory
RoHS Compliant

Certifications

UL 94V0
UL Listed

Product specifications

Special features

Technology type MOV

Material

Thermoplastic

Enclosure

Thermoplastic, UL94V14

Surge current

200 kA

Mounting Method

35 mm DIN rail

Nominal Discharge Current

20 kA

Short-circuit rating

200 kA

Type

Surge arrestor

Operating voltage

600/1200

Indicator type

Remote contact

Frequency rating

50/60 Hz

Operating temperature

-35 to 85 °C

Voltage rating

230/400 Wye (4W+G)

Application

Surge Protection

Degree of protection

IP20

Resources

Catalogs

[BSPMA2240S3GR~240V Corner Gmd Delta, 2P](#)

[Bussmann series complete full line catalog no. 1007](#)

Specifications and datasheets

[Eaton Specification Sheet - BSPMA2240S3GR](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia