Part Number : 444761112
Product Description : Mini-Fit HCS Crimp Terminal, 20-18 AWG, Bag, Copper (Cu) Alloy, Tin (Sn)
Series Number : 44476
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

444761112_sd.pdf

PK-5556-003-001.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-44476-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	44476
Description	Mini-Fit HCS Crimp Terminal, 20-18 AWG, Bag, Copper (Cu) Alloy, Tin (Sn)
Comments	High Current
Product Name	Mini-Fit
UPC	800754367349

Electrical

Current - Maximum per Contact	11.0A

Physical

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.200/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size (AWG)	18, 20

Downloaded from Arrow.com.

Wire Size mm^2	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit Jr. Receptacle Housings	5557
Mini-Fit BMI Dual Row Receptacle Housings	44516
Mini-Fit BMI Dual Row Receptacle Housings	42474

Application Tooling

Global

Description	Part Number
Extraction Tool for Mini-Fit Jr. Terminals	11030044
Extraction Tool for Mini-Fit HCS Terminals, 20-16 AWG	638131200
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 24-18 AWG	638190901

Downloaded from Arrow.com.