



REVISIONS						
		DAP				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	G	REV PER ECR 07-017771	21AUG07	JR	MS	
	H	REVISED PER ECO-19-000777	01OCT2019	RS	DR	



 WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED

- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 TIN PLATE 0.00254 [.000100] MIN THK
PER ASTM B545
- 3 GOLD PLATE PER MIL-G-45204, TYPE II,
CLASS I, 0.00127 [.000050] MIN EXT THK. OVER NICKEL
PLATE 0.00076 [.000030] MIN EXT THK PER SAE AMS QQ-N-290
- 4 COPPER PER ASTM B-152, ANNEALED
- 5 TIN LEAD PLATE (93/7), 0.00254 [.000100]
MIN THK.



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 2.62-6.64mm ² [5,180-13,100] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

240°C [500°F]	500	LOOSE PIECE	N/A		2-322447-1
170°C [338°F]	500	LOOSE PIECE			322447-1
	500	LOOSE PIECE			322447
MAX TEMP.	QTY	PACKAGE TYPE	PRODUCT SPEC	FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93 CHK DA PATTERSON 3-17-93 APVD JL MECKLEY 3-17-93 PRODUCT SPEC SEE TABLE APPLICATION SPEC - WEIGHT -		TE Connectivity NAME TERMINAL, RING TONGUE, SOLISTRAND 12-10 AWG	
DIMENSIONS: MM[INCHES] 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± - FINISH	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL -	SEE TABLE	A2	00779	C=322447	-
		CUSTOMER DRAWING		SCALE 8:1	SHEET 1 of 1
				REV	H