

Data Sheet | Item Number: 210-801

Type labels; 70 x 33 mm; white

<https://www.wago.com/210-801>



Color: ■ white

Similar to illustration

Technical data

Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	500 markers/reel; 1 line
Printing device	Smart Printer (thermal transfer printer)

Physical data

Depth	0.09 mm
Marking surface	33 x 70 mm

Mechanical data

Mounting type	Sticking
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data

Color	white
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Acrylic; permanent
Halogen-free	Yes
Weight	227 g

Environmental requirements

Ambient temperature (storage)	≤+21 °C
Ambient temperature (operation)	-40 ... +150 °C
Relative humidity	40 ... 50 %

Commercial data

Product Group	2 (Terminal Block Accessories)
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143099516
Customs tariff number	39199080888

Product Classification

UNSPSC	55121612
eCl@ss 10.0	27-40-06-29
eCl@ss 9.0	27-40-06-29
ETIM 9.0	EC001288
ETIM 10.0	EC001288
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 210-801	↓
--	---

Documentation

Operating Instructions

210-804 Information on handling print material	1	28.08.2020	pdf	1347.39 KB	↓
--	---	------------	-----	------------	---