


APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/13/06	
A		PART REVISION	4/19/06	
B		ADDED DIM.	8/11/09	
C		UPDATE DRAWING	4/13/18	AY/MY



#### SPECIFICATIONS:

##### Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Natural

Contact: Brass

##### Plating:

Tin over Nickel underplate overall

##### Electrical:

Rated Voltage: 250V AC/DC

Rated Current: 3A AC/DC

Contact Resistance: 20 mohms max.

Insulation resistance: 1,000 Mohms min.

Withstand voltage: 1000V AC for 1 minute.

##### Temperature Rating:

-25°C to +85°C

##### Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20

A = .098 [2.50] x No. of Spaces

B = .098 [2.50] x No. of Spaces + .197 [5.00]

C = .098 [2.50] x No. of Spaces + .138 [3.50]

Assemble state

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED  
 INCHES HOLES  
 $.X \pm .10$   $\emptyset X \pm .10$   
 $.XX \pm .020$   $\emptyset XX \pm .015$   
 $.XXX \pm .015$   $\emptyset XXX \pm .010$

APPROVALS		DATE
DRAWN	LFJ	4/13/06
CHECKED		
APPROVED		

**ADAM  
TECH**  
INTERCONNECTS

909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

WIRE TO BOARD PITCH: 2.5MM  
 WAFER STRAIGHT TYPE W/ KINK

SIZE	PART NO.	REV.
X	25SH-B-XX-TS	C
REF: S00124T	SCALE: NTS	SHEET 1 OF 1