Part Number : 1060597300
Product Description : Optical Industrial Plug Assembly, Metal Body, Outdoor Cable, LC, Multimode, Male
Series Number : 86389
Status : Not Recommended For New Design
Product Category : Fiber Optic Connectors



Documents and Resources

Drawings

1060597300_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Fiber Optic Connectors
Series	86389
Description	Optical Industrial Plug Assembly, Metal Body, Outdoor Cable, LC, Multimode, Male
Mode	Multimode
Product Name	LC
UPC	822350957236

Physical

Angled Physical Contact (APC)	No
Boot Color	N/A
Boot Type	N/A
Cable Size	8.00mm max.
Color - Resin	N/A
Ferrule Hole Size	127µm
Ferrule Material	Ceramic
Gender	Plug
Material - Housing	PEI
Mounting Style	Adhesive
Net Weight	107.470/g
Ports	2
Wire/Cable Type	Round

Solder Process Data

Lead-Free Process Capability	N/A

Downloaded from Arrow.com.