

Datasheet for part number DEMA-9S-F0

Our Catalog Part Number: DEMA-9S-F0
Our Global Manufacturing Part Number: 050909-0011
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*MA

Product Datasheet	
General	D*M High reliable D-Sub Connectors with crimp termination
Wire Gauge Range AWG	Standard: AWG 20-28. High Density: AWG 22-28
Mating Cycles	200
Contact Arrangement	9 contacts size 20
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	10 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	24 hours
Shell Material	steel
Shell Finish	Yellow chromate over zinc
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	white
Gender	Socket
Contacts	delivery without contacts, please order separately
Contact Type	Crimp
Contact Material	copper alloy
Contact Finish	gold over nickel
Hardware	.120" (3,05mm) Through Hole

Specifications and dimensions subject to change.