





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	28AUG2023	ASB	JDB
	D1	DRAWING RE-CREATED IN CREO	26DEC2023	ASB	JDB
	D2	DRAWING CLARIFICATION	02APR2024	ASB	JDB



3D VIEW
SCALE 2:1


INSPECTION LEVEL 1: CONTROL CHART REQUIRED
 (1) PROOF OF PROCESS CAPABILITY OR 100% TEST IF
 PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
(/2) PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

(/3) PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST


1. DRAWING SPECIFICATION ACCORDING TO 5_3_17-DOC-1810-00294
2. COPLANARITY OF ALL CONTACT AND CLIPS $\leq 0,1\text{MM}$

3 PART; 100 PCS. IN BUBBLE BAGS/BULK



 3			
1	-	SOLDER CLIP LEFT	4
1	-	SOLDER CLIP RIGHT	3
4	-	PINS	2
1	-	HOUSING	1
244798-E	REV	DESCRIPTION	ITEM NO.
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY	PARTS LIST		

*VERSION: WITH SEAL, WITHOUT CUT-IN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B S ADRUSH 18AUG2023		TE Connectivity								
DIMENSIONS: mm		CHK M SZELAG 20AUG2023										
	TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 8015		APVD J DE BRUIJN 20AUG2023		NAME M12 MALE, D CODE, 4P, 17MM SMT*							
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-94887									
	MATERIAL - -		APPLICATION SPEC 114-94781		SIZE A 3		CAGE CODE 00779		DRAWING NO C=244798-E		RESTRICTED TO -	
	FINISH -		WEIGHT -		CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1		REV D2	