Pushing Performance
Since 1945

ICC20 Cable-to-Cable

Image is for illustration purposes only. Please refer to product description.

Part number	19 59 120 1020
Specification	ICC20 Cable-to-Cable
HARTING eCatalogue	https://harting.com/19591201020

Identification

Category	Connectors
Series	HARTING ICC
Type of hood/housing	Cable to cable housing

Version

Size	20
Locking type	Bayonet locking
Details	Please order backshell separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP67 IPX9

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	EPDM
Colour (seal)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
Approvals	CE

Commercial data

Packaging size	1
Net weight	55.71 g
Country of origin	India
European customs tariff number	85389099
GTIN	5713140400559
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.