
Part Number : 190990028
Product Description : InsulKrimp Snap Spade for 16-14 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier, Blue
Series Number : 19099
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : BB-2707-06XT



Documents and Resources

Drawings

190990028_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-009-001.pdf

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19099
Description	InsulKrimp Snap Spade for 16-14 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier, Blue
Keyword	Spade Terminal, Spade Terminals
Product Name	InsulKrimp
Style	Spade Snap
Type	Spade Connector
UPC	800753089105

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-0
Insulation	PVC

Downloaded from Arrow.com.

Material - Plating Mating	Tin
Net Weight	0.718/g
Packaging Type	Adhesive Tape on Reel
Stud Size	5-6 (M3-3.5)
Wire Insulation Diameter	4.40mm max.
Wire Size (AWG)	14, 16

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator	638850400

This document was generated on Apr 29, 2026

Downloaded from Arrow.com.