



DCCM100SCBRP

- DESCRIPTION
- SUPPORT
- REQUEST QUOTE
- DOCUMENTS
- 3D DRAWING
- FOOTPRINT/SYMBOL

Share

Commercial PCB Mount Connector | Socket | 100 Positions | Yellow Chromate over Cadmium | Thermoset, Glass-Reinforced, Diallyl Phthalate | Female | 90° PCB | Narrow Profile | Jackpost



Connector Type	Socket
Number of Positions	100
Shell Material	Aluminum alloy
Shell Finish	Yellow Chromate over Cadmium
Insulation Material	Thermoset, Glass-Reinforced, Diallyl Phthalate
Contact Gender	Female
Contact Material	Copper alloy
Contact Finish	Gold
Termination Type	90° PCB
Profile	Narrow
Mounting Hardware	Jackpost
Min Operating Temp. °F (°C)	-65°F (-55°C)
Max Operating Temp. °F (°C)	275°F (135°C)
Current Rating	3 Amps
Withstanding Voltage	600 VAC RMS @ sea level
Contact Resistance	8 mOhm
Max Mating Cycles	500
Contact Insertion Force	6 oz (170 gm)
Contact Withdrawal Force	0.5 oz (14 gm)

BEL GROUPS

- Bel Fuse-Circuit Protection
- Bel Magnetic Solutions

PRODUCTS

- Aviation Spares
- Cable Assemblies

RESOURCES

- Bel Extranet
- Brochures & Catalogs

EXPLORE BEL

- About Us
- Bel Extranet

SOCIAL MEDIA



Bel Power Solutions

Circuit Protection

Cross Reference Tool

Careers



Cinch Connectivity Solutions

Discrete Magnetics

Distributor Stock

Investors

CUI Inc.

High Frequency Magnetics

Order Status

News Room

EOS Power

Integrated Connector Modules

Product Configurators

Signal Transformer

Interconnects

Product Discontinuances

Stewart Connector

Linear Magnetics

Quality & Environment

TRP Connector

Microwave Components

Technical Library

Optical Connectivity

Patching Solutions

Power Supplies

We use cookies to ensure you get the best experience on our website. By using **Belfuse.com**, you agree to our privacy policy. [Learn more](#)

I agree

Decline