



Part Number : [2064600012](#)
Product Description : Micro-Fit+ Crimp
Terminal, Female, 0.38µm Gold (Au) Plating,
30-26 AWG
Series Number : 206460
Status : Active
Product Category : Crimp Terminals



Documents & Resources

Drawings
[2064600012_sd.pdf](#)
[2064600000-PK-000.pdf](#)

Specifications
[2064600001-AS-000.pdf](#)
[2064600000-PS-000.pdf](#)
[2159530000-PS-000.pdf](#)
[2064600000-TS-000.pdf](#)
[2064600001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	206460
Description	Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 30-26 AWG
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Micro-Fit+
UPC	193264161669

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	6.6A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Durability (mating cycles max)	200
Gender	Female
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Net Weight	0.087/g
Packaging Type	Reel
Plating min - Mating	0.380µm
Plating min - Termination	1.520µm
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	1.27mm
Wire Size (AWG)	26, 28, 30
Wire Size mm ²	N/A

Use with Part(s)

Description	Part Number
Micro-Fit+ Dual Row Receptacle Housings	<u>206461</u>
Micro-Fit+ Single Row Receptacle Housings	<u>215759</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Micro-Fit Terminals	<u>11030043</u>
FineAdjust Applicator for Micro-Fit Plus Crimp Terminals, 30-26 AWG, UL1061 Wires	<u>2037023800</u>
FineAdjust Applicator for Micro-Fit Plus Crimp Terminals, 30-26 AWG, UL1007 Wires	<u>2037023900</u>
Hand Crimp Tool for Micro-Fit+ and Micro-Fit TPA Crimp Terminals, 26 AWG, UL1007 and UL1061 Wires	<u>2133094800</u>
Hand Crimp Tool for Micro-Fit+ and Micro-Fit TPA Crimp Terminals, 28 AWG, UL1007 and UL1061 Wires	<u>2133094900</u>
Hand Crimp Tool for Micro-Fit+ and Micro-Fit TPA Crimp Terminals, 30 AWG, UL1007 and UL1061 Wires	<u>2133095000</u>
Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp Terminals, 30-20 AWG	<u>638120800</u>

This document was generated on Mar 22, 2025