



NC3FD-LX-HA

3 pole female receptacle, crimp termination
(Standard B-Crimp), Nickel housing, silver contacts

The DLX series features a compact all metal housing with an ingenious duplex ground contact, which offers excellent RF protection and shielding. It is the ideal match for mating with Neutrik's EMC XLR cable connector.

Features & Benefits

- ✓ All metal housing offers best overall RF protection and electromagnetic shielding
- ✓ Crimp termination with standard B-crimp tool (B-crimp acc. IEC 60352-2)
- ✓ Gastight and Solderless connection (RoHS compliant)
- ✓ New duplex ground contact for excellent contact integrity between chassis and cable connector
- ✓ Unique cage type female contact on 3 pole version increases conductivity and reduces wear on the mated male contact
- ✓ Optional connection to easily join pin1 to chassis ground
- ✓ D-style housing provides installation compatibility with industry standard D mounting dimensions

Technical Information

Product	
Title	NC3FD-LX-HA
Connection Type	XLR
Gender	female

Electrical	
Capacitance between contacts	$\leq 4 \text{ pF}$
Contact resistance	$\leq 5 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact	1 A
Rated voltage	$< 50 \text{ V}$

Mechanical	
Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	> 1000 mating cycles
Wiresize	0.22 - 0.34 mm ²
Wiresize	24 - 22 AWG
Wiring	Crimp contacts
Locking device	Latch lock
Chassis shape	D

Material	
Contact plating	1 µm Ag
Contacts	Bronze (CuSn6)
Insert	PA66
Locking element	Steel Ck67
Locking element plating	Nickel
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel

Environmental	
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Temperature range	-30 °C to +80 °C